



# 3 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco  
Catalog # 3432

3 in. 90 Degree Liquidtight Connector, Uninsulated

## Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3432
Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034323

## Dimensions

Dimensions	4.75 in x 4.75 in x 10.625 in
Height	10.625 in
Length	4.75 in
Trade Size	3 in
Weight	8.35 lb



\*Representative Image

Width 4.75 in

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	192

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3432 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3432](#)
- [Specifications - 3432 Specification Sheet](#)
- [Specifications - 3432 Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)