



1-1/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco
Catalog # 3515-3



*Representative Image

1-1/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3515-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169351536

Dimensions

Dimensions	1.875 in x 2.188 in x 2.188 in
Height	2.188 in
Length	1.875 in
Trade Size	1-1/4 in
Weight	0.688 lb
Width	2.188 in

Electrical Ratings

Grounding Wire Capacity	#4 STR
Maximum	
Grounding Wire Capacity	#14 SOL
Minimum	

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2940

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC-E195975-4](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 35153 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3515-3 Specification Sheet](#)
- [Specifications - 3515-3 Specification Sheet French](#)
- [Specifications - 3515-3](#)
- [Terms and Conditions - HCC Terms & Conditions](#)