



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Eight 1/2 in. KO's

By Raco
Catalog # 561



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Eight 1/2 in. KO's

Features

- 3 in. x 2 in., 2-3/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- 14 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	561
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005613
Wiring System	Conduit

Dimensions

Actual Depth	2.75 in
Cubic Capacity	14 cu.in

Depth	2.75 in
Height	3.375 in
Weight	0.567 lb
Width	2 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2750

Product Assets

[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 3](#)
[Certifications - UL COC - E195978-18](#)
[Sales Drawings - 561 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 561](#)
[Specifications - 561 Specification Sheet French](#)
[Specifications - 561 Specification Sheet](#)
[Terms and Conditions - HCC Terms & Conditions](#)