



58505KIT

By Raco

Catalog # 58505KIT

Generator Hook-Up Box Kit, includes 50A 125/250V, 3-Pole 4-Wire Grounding Steel Zinc plated flanged inlet, Weatherproof box, extension ring, adapter, gaskets, screws, closure plugs and mounting lugs.

Features

- Locking Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminal, White
- Backwired terminations for ease of installation
- Eight box mounting options with detachable lugs
- #8 Multiple drive terminal screws (Slotted, Phillips, Robertson) and Mounting screws
- 2 Gang Weatherproof box, Gray, in rugged die cast aluminum construction and state-of-the-art powder coat finish to provide maximum weatherability and scratch resistance. Five 1 in. threaded outlets. Six closure plugs and gaskets included.
- Metallic flanged Inlet casing provides maximum strength and protection. Its thermoset interior provides superior heat resistance
- No need to purchase separate components
- Installation hardware, gasket and multilingual instructions included

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

General

Catalog Number	58505KIT
Number Of Poles	3 - Pole
UPC	805035054772



Dimensions

Dimensions	5.25 in x 4.66 in x 4.66 in
Height	4.66 in
Length	5.25 in
Weight	2.95 lb
Width	4.66 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Wire Size	#10 AWG to #6 AWG
-----------	-------------------

Product Assets

[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Installation Manuals - Generator kit 50A Installation Manual](#)
[Installation Manuals - Generator kit 50A Installation Manual French](#)
[Sales Drawings - Blow Out Drawing](#)
[Sales Drawings - 58505KIT_SalesDrawings](#)
[Specifications - 58505KIT Specification Sheet French](#)
[Specifications - 58505KIT Specification Sheet English](#)
[Specifications - 58505KIT_spec](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
RACO_CA-58505KIT-SPEC-EN | REV 4/2025