



# Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Black Finish

By Raco  
Catalog # 6239BK



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Black Finish

### Features

- Can be used for power/data
- 15A, 125V tamper resistant receptacle
- Removable neoprene gaskets allow for independent use of either side of the receptacle with cover closed
- Recessed receptacle minimizes plug protrusion
- Height accessible adjustments after box is mounted

### General

Catalog Number	6239BK
Cover Shape	Round
Cover Type	Round
EU RoHS Indicator	Contact Manufacturer
Material	Steel
Number of Gang(s)	1-Gang
Size	1-Gang
Type of Use	Wood
UPC	050169947128

### Dimensions

Cubic Capacity	28 cu.in
Dimensions	5.6 in x 5.6 in x 5.3 in
Height	5.3 in
Length	5.6 in

Weight	2.354 lb
Width	5.6 in

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
------------------	---

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	200

### Product Assets

- [360 Product View - RACO\\_6239BK](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Floor Boxes](#)
- [Installation Manuals - 6239 Series Instruction Sheet](#)
- [Sales Drawings - 6239BK Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Floor Boxes for Structural Wood Floors](#)
- [Specifications - 6239BK Specification Sheet English](#)
- [Specifications - 6239BK Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - How to Choose the Correct Floor Box](#)