



1-Gang Masonry Box, Gangable, 3-1/2 in. Deep, Ten TKO's

By Raco
Catalog # 689



1-Gang Masonry Box, Gangable, 3-1/2 in. Deep, Ten TKO's

Features

- Rugged welded design does not fall apart during construction.
- Gangable design allows installer to build unlimited number of gangs to hold multiple devices.
- Rectangular shape fits square cuts in block.
- Standard 1/2" and 3/4" TKO® knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #675 fits 2-1/2" and #676 fits 3-1/2" depth.
- Forward mounted grounding provision allows for easy installation of grounding pigtail.
- Standard wall plates can be used.
- Supplied with ten 1/2 and 3/4 in. concentric knockouts
- Gangable design allows construction of multiple gang box from one product
- Ground is located near the front of the box for installer's convenience
- 22.5 cu. in. capacity
- For 6, 8, and 10 in. block walls

General

Bracket Type	No Bracket
Catalog Number	689
EU RoHS Indicator	Contact Manufacturer
Gangable	Yes
Knockouts	1/2 in - 3/4 in Combination (TKO)

Material	Steel
Number of Gang(s)	1-Gang
UPC	050169006894

Dimensions

Cubic Capacity	22.5 cu.in
Depth	3.5 in
Height	3.75 in
Weight	0.842 lb
Width	1.938 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	2000

Product Assets

[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Sales Drawings - 689 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 689 Specification Sheet French](#)
[Specifications - 689 Specification Sheet](#)
[Specifications - 689](#)
[Terms and Conditions - HCC Terms & Conditions](#)