



1-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Eight Concentric KO's

By Raco
Catalog # 690



1-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Eight Concentric KO's

Features

- Rugged welded design does not fall apart during construction.
- Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths.
- Rectangular shape fits square cuts in block.
- Large volume design allows for additional work room inside the box.
- Standard 1/2" and 3/4" concentric knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths.
- Standard wall plates can be used.
- Supplied with eight 1/2 & 3/4 in. concentric knockouts
- Welded steel construction
- Standard device spacing with tapped 6-32 holes for devices
- 16 cu. in. capacity
- For 4 in. block walls

General

Bracket Type	No Bracket
Catalog Number	690
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Gangable	No
Knockouts	1/2 - 3/4 in Concentric
Material	Steel
Number of Gang(s)	1-Gang

UPC 050169006900

Dimensions

Cubic Capacity	16 cu.in
Depth	2.5 in
Height	3.75 in
Weight	0.63 lb
Width	1.969 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2250

Product Assets

[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-9](#)
[Sales Drawings - 690 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 690 Specification Sheet French](#)
[Specifications - 690 Specification Sheet](#)
[Specifications - 690](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand