



3 in. x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Nine 1/2 in. KO's, Plaster Ears

By Raco
Catalog # [8590](#)



3 in. x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Nine 1/2 in. KO's, Plaster Ears

Features

- 3 in. x 2 in., 3-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with nine 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 18 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	8590
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005903
Wiring System	Conduit

Dimensions

Cubic Capacity	18 cu.in
Depth	3.5 in
Height	4.219 in
Weight	0.736 lb
Width	2 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2100

Product Assets

[360 Product View - RACO_8590](#)
[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Specifications - 8590](#)
[Specifications - 8590 Specification Sheet](#)
[Specifications - 8590 Specification Sheet French](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand