



4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's

By Raco
Catalog # 8650



4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's

Features

- Welded construction
- 4 in. x 2 in., 1-1/2 in. deep
- Supplied with eleven 1/2 in. knockouts
- 11.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	8650
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006504
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	11.5 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	No
Weight	0.478 lb

Width 2.125 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed cULus Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3600

Product Assets

[360 Product View - RACO_8650](#)
[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 8](#)
[Certifications - NEMA OS1](#)
[Certifications - LEED Statement](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Specifications - 8650 Specification Sheet English](#)
[Specifications - 8650 Specification Sheet French](#)
[Specifications - 8650 Specification Sheet](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand