

by Wiegmann Catalog ID: RHC483612

N3R Continuous Hinge Wall-Mount 48X36X12 Carbon Steel - Gray

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor installations gainst rain, sleet, and snow, or indoors against dripping water.

Bodies and doors fabricated from 14 gauge carbon steel. Continuous hinge. Hinge is made of
galvanized steel with a stainless steel pin. No knockouts. Collar studs provided for mounting optional
back panels. External mounting plates, top and bottom of enclosure. Hasp and staple provided for
padlocking. Grounding provisions provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provides protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Seam and Tack Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Туре	Enclosure
UPC	786725407118

Dimensions

Cubic Capacity	20736 cu.in
Depth	12 in
Height	48 in
Weight	153 lb

Width	36 in	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	NEMA 3R	
UL Listed	Yes	