


RIGID BODIES AND ASSEMBLIES

LB Assembly
N/A

C13



Catalog #: RLB100

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

DRAWING DIMENSIONS

- Dimension A: 5.92 in.
- Dimension B: 1.82 in.
- Dimension C: 2.78 in.
- Dimension D: 4.830 in.
- Dimension E: Tapped holes #8-32UNC-2B
- Thread Spec. F: 1-11 1/2NPT
- Dimension G: 1.039 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm3): 12.0 (196.6)

PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 5
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 62.00
- Ship Carton Length (in.): 7.00
- Ship Carton Width (in.): 4.75
- Ship Carton Height (in.): 8.13
- Ctn Weight (Lbs.): 3.10
- UPC Number: 092326211932
- I2of5: 30092326211933