




RIGID BODIES AND ASSEMBLIES

LB Assembly
N/A

C13



Catalog #: RLB300

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3 in.

DRAWING DIMENSIONS

- Dimension A: 12.83 in.
- Dimension B: 4.49 in.
- Dimension C: 5.91 in.
- Dimension D: 11.250 in.
- Dimension E: Tapped holes #5/16UNC-2B
- Thread Spec. F: 3-8NPT
- Dimension G: 3.058 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm3): 179.8 (2946.4)

PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 1
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 450.00
- Ship Carton Length (in.): 14.13
- Ship Carton Width (in.): 5.88
- Ship Carton Height (in.): 6.88
- Ctn Weight (Lbs.): 4.50
- UPC Number: 092326213110
- I2of5: 30092326213111