# RACO' TAYMAC' BELL'


# **RIGID BODIES AND ASSEMBLIES**

# LB Assembly N/A

C13

www.hubbell.com





Catalog #: RLB400

#### APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors. N/A

# PRODUCT FEATURES

Durable die cast aluminum construction Premium powder coat finish Includes NBR synthetic rubber gasket Stamped aluminum cover Combination head screw

# UL LISTED

File E331564

#### NEMA

NEMA 3R rated

# NEC

2014 NEC® compliant

# GENERAL PRODUCT INFORMATION

Trade Size:

# DRAWING DIMENSIONS

Dimension A: Dimension B: Dimension C: Dimension D: Dimension E: Thread Spec. F: Dimension G:

# PRODUCT MEASUREMENTS Cubic Inches (cm3):

PACKAGING

Package Type: Ship Carton Qty.: Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): Ship Carton Height (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): UPC Number: I2of5: 4 in. 15.65 in. 5.55 in. 7.09 in. 13.687 in. Tapped holes #5/16UNC-2B 4-8NPT 4.016 in.

323.0 (5293.0)

Carton 1 Yes 770.00 16.88 7.88 7.13 7.70 092326213134 30092326213135