


RIGID BODIES AND ASSEMBLIES

LL Assembly N/A

C13





Catalog #: RLL075

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

PRODUCT FEATURES

Durable die cast aluminum construction Premium powder coat finish Includes NBR synthetic rubber gasket Stamped aluminum cover Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

DRAWING DIMENSIONS

5.08 in. 2.30 in. 1.63 in. Dimension A: Dimension B: Dimension C: Dimension D: 1.56 in. Dimension E:

4.125 in. Tapped holes #8-32UNC-2B Dimension F: 3/4-14NPT

Dimension G: Dimension H: .814 in.

PRODUCT MEASUREMENTS

7.3 (119.6) Cubic Inches (cm3):

PACKAGING

Package Type:
Ship Carton Qty.:
Product UPC-A Labeled:
Weight (Lbs. Per/C): Carton Yes 44.00 5.75 4.25 6.50 Ship Carton Length (in.): Ship Carton Width (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): UPC Number: 2.20

092326213233 12of5: 30092326213234