

RLS500-6I

by CMC
Catalog ID: RLS500-6I



Stud-mount transformer connectors, allows left or right-hand mounting, Dual rated connectors for Aluminum or Copper conductors, Insulated Stud-Mount Connectors

- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class ‘A’ connectors.
- Supplied with radial-tipped set-screws.
- Offers fast, economical, reusable, and dependable connections for right or left hand installations.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9” insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663084616

Dimensions

Height	2.73 in
Length	9.39 in
Width	3 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
-----------------	---------------------

Number Of Conductors	6
----------------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
RUS Listed Reference	Yes