

# RLSS500-4SLI

by CMC  
Catalog ID: RLSS500-4SLI



Stud-mount transformer connectors, allows left or right-hand mounting, Dual rated connectors for Aluminum or Copper conductors, Insulated Stud-Mount Connectors, Street light tap available

- RLSS with patented Keyhole mounting.
- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class ‘A’ connectors.
- Supplied with radial-tipped set-screws.
- Offers fast, economical, reusable, and dependable connections for right or left hand installations.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9” insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

## Product Details

### General

|          |                         |
|----------|-------------------------|
| Material | Aluminum Alloy, 6061-T6 |
| UPC      | 192663084890            |

### Dimensions

|        |         |
|--------|---------|
| Height | 2.73 in |
| Length | 6.99 in |
| Width  | 3 in    |

### Electrical Ratings

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

### Conductor Related

|                      |                     |
|----------------------|---------------------|
| Conductor Range      | 500 Kcmil - #10 AWG |
| Number Of Conductors | 4                   |



**CONNECTOR MANUFACTURING COMPANY**

3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

