


# **RIGID BODIES AND ASSEMBLIES**

T Assembly

C13





Catalog #: RLT100

#### **APPLICATIONS**

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

## PRODUCT FEATURES

Durable die cast aluminum construction Premium powder coat finish Includes NBR synthetic rubber gasket Stamped aluminum cover Combination head screw

## UL LISTED

File E331564

# NEMA

NEMA 3R rated

## NEC

2014 NEC® compliant

# GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

# DRAWING DIMENSIONS

Dimension A: 6.46 in. 2.68 in. Dimension B: 1.89 in. Dimension C: Dimension D: 1.82 in. Dimension E: 4.83 in.

Dimension F: Tapped holes #8-32UNC-2B

Dimension G: Dimension H: 1-11 1/2NPT 1.039 in.

PRODUCT MEASUREMENTS

12.0 (196.6) Cubic Inches (cm3):

## **PACKAGING**

Package Type:
Ship Carton Qty.:
Product UPC-A Labeled:
Weight (Lbs. Per/C): Carton Yes 60.00 Ship Carton Length (in.): 7.00 Ship Carton Width (in.): Ship Carton Height (in.): 4.50 8.00 Ctn Weight (Lbs.): UPC Number: 3.00

092326213424 12of5: 30092326213425