



RLUS500-6I

by CMC

Catalog ID: RLUS500-6I

Space-saver stud-mount transformer connectors allows left or right-hand mounting, Screw-On, Dual rated connectors for Aluminum or Copper conductors

- Clear plated for low-contact resistance.
- Allows left or right-hand installation.
- Fully tested to ANSI C119.4 for Class 'A' connector.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- 105°C Rated clear plastisol cover.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of an insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.
- Designed to reduce cantilever stress on the busing by 50% and increase available safe space.
- For use on both 5/8" and 1" studs in screw-on and quick-disconnect models.

Product Details

General

Material	Aluminum Alloy, 6061-T6
Type	RLUSS/RLUS
UPC	192663076215

Dimensions

Dimensions	8.66 in x 2.88 in x 4.6 in
Height	4.6 in
Length	8.66 in
Width	2.88 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
Number Of Conductors	6

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
RUS Listed Reference	Yes



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: jrex@cmclugs.com

