

Catalog #293

4 IN. ROUND CEILING PAN

DRAWN WITH CONDUIT KO'S, 1/2 IN. DEEP

FEATURES

- Rated for 50 lb. fixture support
- Combination screw heads provide for faster installation
- L clamps provided for Nonmetallic Sheathed Cable (NMSC)
- Supplied with five 1/2 in. knockouts
- 6.0 cu. in. capacity
- Do not use to support ceiling fans

APPLICATIONS

RACO® Ceiling Pans are used in the installation of ceiling or wall lighting fixtures

CERTIFICATIONS



File E195978

COMPLIANCES

MSDS

 $www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf$



7,148,420; 4,892,211

OTHER PATENTS

Canada 1,324,360; Mexico 166.125

PACKAGING

MINIMUM CARTON QTY.:	50
PRODUCT UPC-A LABELED:	No
WEIGHT (LBS. PER/C):	33.50
SHIP CARTON LENGTH (IN.):	12.88
SHIP CARTON WIDTH (IN.):	5.63
SHIP CARTON HEIGHT (IN.):	8.75
CTN WEIGHT (LBS.):	16.75

UPC NUMBER: 050169902936 I2OF5: 50050169902931

DRAWING MEASUREMENTS

DIMENSION A:	1/2 IN.
DIMENSION B:	4.00 IN.
CUBIC INCHES:	6.0
WT. EA. (LBS.):	0.335
PRODUCT LENGTH (IN.):	0.56