

RSC060604

by Wiegmann Catalog ID: RSC060604

N3R Screw-Cover Wall-Mount 6X6X4 Carbon Steel - Gray

RSC SERIES - 16 GAUGE CARBON STEEL NEMA 3R SCREW COVER WALL-MOUNT -ENCLOSURE SIZE 6-1/8 IN X 6-1/8 IN X 4-3/16 IN.

 Bodies and doors fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides and front. Knockouts are standard on bottom. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General Application Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water. Color Gray Construction Spot Welded Cover Type Screw Cover Finish Type Textured Knockouts Yes Listings UL, CSA Carbon Steel Material Mounting Method Embossed Mounting Holes Mounting Type Wall Mount Enclosure Туре 786725400157 UPC

Dimensions

Cubic Capacity	144 cu.in
Depth	4 in
Height	6 in
Weight	4.1 lb
Width	6 in

Conductor Related

e Entry	Knock Outs
---------	------------

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	NEMA 3R
UL Listed	Yes