



RSC060604NK

by Wiegmann

Catalog ID: RSC060604NK

N3R Screw-Cover Wall-Mount No Knockouts 6X6X4 Carbon Steel - Gray

RSC SERIES - 16 GAUGE CARBON STEEL NEMA 3R SCREW COVER WALL-MOUNT - NOKNOCKOUTS
- ENCLOSURE SIZE 6-1/8 IN X 6-1/8 IN X 4-3/16 IN.

- Bodies and doors fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides and front. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725860883

Dimensions

Cubic Capacity	144 cu.in
Depth	4 in
Height	6 in
Weight	4 lb
Width	6 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	NEMA 3R
UL Listed	Yes