

RSC101006

by Wiegmann Catalog ID: RSC101006

N3R Screw-Cover Wall-Mount 10X10X6 Carbon Steel - Gray

RSC SERIES - 16 GAUGE CARBON STEEL NEMA 3R SCREW COVER WALL-MOUNT -ENCLOSURE SIZE 10-1/8 IN X 10-1/8 IN X 6-3/16 IN.

Bodies and doors fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides
and front. Knockouts are standard on bottom. A slip-on reversible cover is securely fastened with
screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is
provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Textured
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Туре	Enclosure
UPC	786725402458

Dimensions

Nema Rating
UL Listed

Cubic Capacity	600 cu.in
Depth	6 in
Height	10 in
Weight	10 lb
Width	10 in
Conductor Related	
Cable Entry	Knock Outs
Certifications and Compliance	
Certified Listed	• UL • CSA

NEMA 3R

Yes