

RSC101206G

by Wiegmann Catalog ID: RSC101206G

N3R Screw-Cover Wall-Mount 10X12X6 Carbon Steel - Galvanized

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.

Bodies and doors fabricated from 16 gauge pre-galvanized steel. Drip shield top and smooth seamless
sides and front. Knockouts are standard on bottom. A slip-on reversible cover is securely fastened with
screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is
provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Туре	Enclosure
UPC	786725402526

Dimensions

Cubic Capacity	720 cu.in
Depth	6 in
Height	12 in
Weight	11.6 lb
Width	10 in
Conductor Related	
Cable Entry	Knock Outs
Certifications and Compliance	
Certified Listed	• UL • CSA
Nema Rating	NEMA 3R
UL Listed	Yes