



* Representative image

RSC121208GNK

by Wiegmann
Catalog ID: RSC121208GNK

Prop65_Cancer&Reproductive

N3R Screw-Cover Wall-Mount No Knockouts 12X12X8 Carbon Steel - Galvanized

- Bodies and doors fabricated from 16 gauge pre-galvanized steel. Drip shield top and smooth seamless sides and front. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

| | |
|-----------------|---|
| Application | Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water. |
| Construction | Spot Welded |
| Cover Type | Screw Cover |
| Finish Type | Galvanized |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Steel, Pre-Galvanized |
| Mounting Method | Embossed Mounting Holes |
| Mounting Type | Embossed Mounting Holes |
| Type | Enclosure |
| UPC | 786725875498 |

Dimensions

| | |
|----------------|------------|
| Cubic Capacity | 1152 cu.in |
| Depth | 8 in |
| Height | 12 in |
| Weight | 13 lb |
| Width | 12 in |

Certifications and Compliance

| | |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none"> UL CSA |
| Nema Rating | 3R |
| UL Listed | Yes |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|