



RSC151806G

by Wiegmann
Catalog ID: RSC151806G

N3R Screw-Cover Wall-Mount 15X18X6 Carbon Steel - Galvanized

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.

- Bodies and doors fabricated from 16 gauge pre-galvanized steel. Drip shield top and smooth seamless sides and front. Knockouts are standard on bottom. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

| | |
|-----------------|---|
| Application | Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water. |
| Construction | Spot Welded |
| Cover Type | Screw Cover |
| Finish Type | Galvanized |
| Knockouts | Yes |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Embossed Mounting Holes |
| Mounting Type | Wall Mount |
| Type | Enclosure |
| UPC | 786725845958 |

Dimensions

| | |
|----------------|------------|
| Cubic Capacity | 1620 cu.in |
| Depth | 6 in |
| Height | 18 in |
| Weight | 17.5 lb |
| Width | 15 in |

Conductor Related

| | |
|-------------|------------|
| Cable Entry | Knock Outs |
|-------------|------------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 3R |
| UL Listed | Yes |