



RSC242406NK

by Wiegmann
Catalog ID: RSC242406NK

N3R Screw-Cover Wall-Mount No Knockouts 24X24X6 Carbon Steel - Gray

- Bodies and doors fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides and front. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725865154

Dimensions

Cubic Capacity	3456 cu.in
Depth	6 in
Height	24 in
Weight	45 lb
Width	24 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	3R
UL Listed	Yes