

by Wiegmann Catalog ID: RSCG060624

N3R Gutter 6X6X24 Carbon Steel - Gray

 Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge. Knockouts are provided on bottom of enclosure.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Туре	Gutter
UPC	786725408559

Dimensions

Actual Depth	24.13 in
Actual Height	6.060 in
Cubic Capacity	864 cu.in
Depth	24 in
Height	6 in
Weight	13.5 lb
Width	6 in

Conductor Related

Cable Entry	Knock Outs	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	3R	
UL Listed	Yes	