



RSCG060636NK

by Wiegmann
Catalog ID: RSCG060636NK

N3R Gutter - No Knockouts 6X6X36 Carbon Steel - Gray

- Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725863419

Dimensions

Actual Depth	36.13 in
Actual Height	6.060 in
Actual Width	6.060 in
Cubic Capacity	1296 cu.in
Depth	36 in
Height	6 in
Weight	19 lb
Width	6 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	3R
UL Listed	Yes