



RSCG080824NK

by Wiegmann
Catalog ID: RSCG080824NK

N3R Gutter - No Knockouts 8X8X24 Carbon Steel - Gray

- Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725863495

Dimensions

Actual Depth	24.13 in
Actual Height	8.060 in
Cubic Capacity	1920 cu.in
Depth	24 in
Height	8 in
Weight	18 lb
Width	10 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	3R
UL Listed	Yes