



## RSCG080836GNK

by Wiegmann  
Catalog ID: RSCG080836GNK

N3R Gutter - No Knockouts 8X8X36 Carbon Steel - Galvanized

- Trough and cover fabricated from 16 gauge G-90 pre-galvanized steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

### Product Details

#### General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Construction	Spot and Tack Welded
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725863525

#### Dimensions

Actual Depth	36.13 in
Actual Height	8.060 in
Actual Width	8.060 in
Cubic Capacity	3456 cu.in
Depth	36 in
Height	8 in
Weight	25 lb
Width	12 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	3R
UL Listed	Yes