

RSCG101060

by Wiegmann Catalog ID: RSCG101060

N3R Gutter 10X10X60 Carbon Steel - Gray

• Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge. Knockouts are provided on bottom of enclosure.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Туре	Gutter
UPC	786725874989

Dimensions

Actual Depth	60.13 in
Actual Height	10.060 in
Cubic Capacity	6000 cu.in
Depth	60 in
Height	10 in
Weight	31 lb
Width	10 in

Conductor Related

Cable Entry	Knock Outs	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	3R	
UL Listed	Yes	