

by Wiegmann Catalog ID: RSCG121248

N3R Gutter 12X12X48 Carbon Steel - Gray

• Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge. Knockouts are provided on bottom of enclosure.

## **Product Details**

## General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Туре	Gutter
UPC	786725875092

## Dimensions

Actual Depth	48.130 in
Actual Height	12.060 in
Actual Length	48.13 in
Actual Width	12.060 in
Cubic Capacity	6912 cu.in
Depth	48 in
Height	12 in
Weight	28 lb

Width	12 in	
Conductor Related		
Cable Entry	Knock Outs	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	3R	
UL Listed	Yes	