



RSCG121248NK

by Wiegmann
Catalog ID: RSCG121248NK

N3R Gutter - No Knockouts 12X12X48 Carbon Steel - Gray

- Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725875337

Dimensions

Actual Depth	48.130 in
Actual Height	12.060 in
Actual Length	48.13 in
Actual Width	12.060 in
Cubic Capacity	6912 cu.in
Depth	48 in
Height	12 in
Weight	60 lb

Width	12 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	3R
UL Listed	Yes