




RIGID BODIES AND ASSEMBLIES

Service Entrance Elbow
N/A

C13



CATALOG NUMBER	CONDUIT SIZE	A	B	C
RSLB050	1/2"	1.587	1.366	3.26
RSLB075	3/4"	1.878	1.693	3.663
RSLB100	1"	2.087	1.917	4.272
RSLB125	1-1/4"	2.579	2.39	5.506
RSLB150	1-1/2"	2.997	2.654	6.217
RSLB200	2"	3.075	3.122	6.715



Catalog #: RSLB100

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

PRODUCT FEATURES

Durable die cast aluminum construction
Premium powder coat finish
Includes NBR synthetic rubber gasket
Stamped aluminum cover
Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

DRAWING DIMENSIONS

Dimension A: 2.087 in.
Dimension B: 1.917 in.
Dimension C: 4.272 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 3
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 43.30
Ship Carton Length (in.): 6.75
Ship Carton Width (in.): 3.63
Ship Carton Height (in.): 7.13
Ctn Weight (Lbs.): 1.30
UPC Number: 092326212472
I2of5: 30092326212473