

# SC121204

by Wiegmann Catalog ID: SC121204

N1 Screw-Cover 12X12X4 Carbon Steel - Gray

SC SERIES - 16 GAUGE CARBON STEEL NEMA 1 SCREW COVER WALL-MOUNT WITHKNOCKOUTS - ENCLOSURE SIZE 12-1/8 IN X 12-1/8 IN X 4-3/16 IN.

Fabricated from 16 gauge steel. Flat, removable covers fastened with plated steel screws. Cover design
permits easy removal without extracting cover screws. Mounting holes on back of box. Removable
concentric knockouts on all four sides.

## **Product Details**

### General

| Application     | Designed for use as a junction box and pull box in commercial and general industrial applications. Flush covers must be ordered separately for flush mount applications. |
|-----------------|--|
| Color           | Gray   |
| Construction    | Spot Welded  |
| Cover Type      | Screw Cover  |
| Finish Type     | Textured   |
| Knockouts       | Yes  |
| Listings        | UL, CSA  |
| Material        | Carbon Steel   |
| Mounting Method | Embossed Mounting Holes  |
| Mounting Type   | Wall Mount   |
| Туре            | Enclosure  |
| UPC             | 786725313907   |

#### Dimensions

| Actual Height | 12.125 in |
|---------------|-----------|
| Actual Width  | 12.125 in |
| Depth         | 4 in      |
| Height        | 12 in     |
| Weight        | 9 lb      |
| Width         | 12 in     |

#### Conductor Related

| Cable Entry | Knock Outs |
|-------------|------------|
|             |            |

## Certifications and Compliance

| Certified Listed | • UL<br>• CSA |
|------------------|---------------|
| Nema Rating      | NEMA 1        |
| UL Listed        | Yes           |