



SC161604G

by Wiegmann
Catalog ID: SC161604G

N1 Screw-Cover 16X16X4 Carbon Steel - Galvanized

SC SERIES - GALVANIZED STEEL NEMA 1 SCREW COVER WALL-MOUNT ENCLOSURE WITH KNOCKOUTS - ENCLOSURE SIZE 16-1/8 INCH X 16-1/8 INCH X 4-3/16 INCH.

- Fabricated from 16 gauge G-90 pre-galvanized steel. Flat, removable covers fastened with plated steel screws. Cover design permits easy removal without extracting cover screws. Mounting holes on back of box. Removable concentric knockouts on all four sides.

Product Details

General

Application	Designed for use as a junction box and pull box in commercial and general industrial applications. Flush covers must be ordered separately for flush mount applications.
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725875474

Dimensions

Actual Depth	4.188 in
Actual Height	16.125 in
Actual Width	16.125 in
Depth	4 in
Height	16 in
Weight	13.5 lb
Width	16 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 1
UL Listed	Yes