



SDN12603812A

by Wiegmann
Catalog ID: SDN12603812A

N12 Single Door Flanged Disconnect No Handle Special Plate 60X38X12 Carbon Steel - Gray

Product Details

General

Application	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers.
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External mounting feet
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725865543

Dimensions

Actual Depth	12.13 in
Actual Width	37.38 in
Depth	12 in
Height	60 in

Weight	175 lb
Width	37 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	12
UL Listed	Yes