

# SDQ350-4I

by CMC

Catalog ID: SDQ350-4I



Space-saver stud-mount transformer connectors

- Clear plated for low-contact resistance
- Fully tested to ANSI C1194 for Class 'A' connectors
- Offers fast, economical, reusable, and dependable connections
- Supplied with aluminum radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench
- A torque wrench should be used to ensure the proper torque is achieved

## Product Details

### Dimensions

Height	2.5 in
Length	5.55 in
Width	1.38 in

### Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------