



# SG-1000

by CMC  
Catalog ID: SG-1000

Dual Rated Solderless Connector, wire range 1000 AWG -350 AWG. TYPE:SG.CMC® Switchgear connectors are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. Designed with slotted mounting holes on 350MCM and above for varied mounting arrangements. 90° C Rated (486B Listed). UL listed and CSA certified.

## Product Details

### General

Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	192663018277

### Dimensions

Height	1.88 in
Length	6.19 in
Width	1.62 in

### Conductor Related

Conductor - Copper Str Size Range	1000-350 Kcmil
-----------------------------------	----------------