



SG-500

by CMC
Catalog ID: SG-500

Dual Rated Solderless Connector, wire range 500 AWG -2 AWG. TYPE:SG.CMC® Switchgear connectors are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. Designed with slotted mounting holes on 350MCM and above for varied mounting arrangements. 90° C Rated (486B Listed). UL listed and CSA certified.

Product Details

General

Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	192663018253

Dimensions

Height	1.56 in
Length	4.69 in
Width	1.25 in

Conductor Related

Conductor - Copper Str Size Range	500 Kcmil-2 AWG
-----------------------------------	-----------------