

SH8-350SLXB

by CMC
Catalog ID: SH8-350SLXB



Space-saver stud-mount transformer connectors, offset, compact secondary transformer stud connectors with patented keyhole mounting, Dual rated connectors for Aluminum or Copper conductors, Slip fit

- Street light port furnished as standard.
- Supplied with 6262-T9 alloy aluminum radial-tipped screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes inhibitor in all ports and stud-mounting hole.
- Fully tested to ANSI C119.4 for Class 'A' connectors.

Product Details

General

Material	Aluminum Alloy, 6061-T6
Number Of Outlets	8
UPC	192663117253

Dimensions

Length	2.12 in
Width	5.32 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------