

SHB10-350SLXB

by CMC

Catalog ID: SHB10-350SLXB



Space-saver stud-mount transformer connectors, offset, compact secondary transformer stud connectors with sharkbite™ features, Dual rated connectors for Aluminum or Copper conductors, Quick disconnect

- Street light port furnished as standard.
- Supplied with aluminum radial-tipped screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes inhibitor in all ports and stud-mounting hole.
- Patented Two-In-One Shark-Bite™ mounting hole feature allows the connector to fit on a 5/8"-11 or 1"-14 transformer stud. Both stud sizes fit in the same hole.
- Shark-Bite™ mounting hole feature provides 10 times the surface area contact on the stud over traditional connectors.
- The Shark-Bite™ feature also securely locks the connector onto the stud to eliminate wobble when installing the conductors.
- Fully tested to ANSI C119.4 for Class 'A' connectors.

Product Details

General

Material	Aluminum Alloy, 6061-T6
Number Of Outlets	10
UPC	192663114542

Dimensions

Length	7.39 in
Width	2.73 in

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

