



# SR-750

by CMC  
Catalog ID: SR-750

Splicers / Reducers, Type: SR- Solid Bearers, conductor range: 750 AWG-250 AWG.Al/Cu Rated.CMC®  
Splicers/Reducers are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. The rounded corners facilitate tapping and a solid center barrier prevents dissimilar metals from coming into contact.90° C Rated (486B Listed). UL listed and CSA certified.

## Product Details

### General

Material	Aluminum
UPC	192663015023

### Dimensions

Height	1.75 in
Length	6.25 in
Width	1.63 in

### Conductor Related

Conductor - Copper Str Size Range	750-250 Kcmil
-----------------------------------	---------------