



SSJW62

by Wiegmann
Catalog ID: SSJW62

N4X Hinged Wireway 6X6X24 304 Stainless Steel

Product Details

General

Accessory Type	Wireway
Application	Designed to protect electrical wiring in areas where corrosion problems exist.
Color	Stainless Steel
Cover Type	Hinged Cover
Enclosure Type	Nema 4X & 12 Type Enclosure
Finish Type	Smooth Grained
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Type	Wireway
UPC	786725482108

Dimensions

Actual Length	24.000 in
Depth	24 in
Height	6 in
Weight	18 lb

Width	6 in
-------	------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • CSA
Nema Rating	4X
UL Listed	Yes