



Anchor, Tough One, 10in, 15,000 ft-lb rating, 2.5in hub, 1in threads, bevel leading edge

by CHANCE Utility
Catalog ID: T1025061

Tough One Anchor Helix, 15,000 Ft Lbs (20,340 N-M), 10" (254 mm) beveled leading edge helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint



* Representative image

Product Details

General

Coating	Painted
Number of Helices	1
Torque Rating	15000 ft-lbs
Type	Anchor Helix
UPC	096359460152

Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	2.500 in
Rod Diameter	<ul style="list-style-type: none"> • 0.750 • 1.000 in
Weight	16.023 lb

Logistics

Carton Quantity	3 EA
Pallet Quantity	144 EA
Standard Package	3

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com