



## T1150V0370BC

by Acme Electric  
Catalog ID: T1150V0370BC

Buck-Boost Transformer Single Phase 277 - 12/24V, 150kVA

### Product Details

#### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	12/24 V
Winding Material	CU

#### Dimensions

Height	7.12 in
Length	3.62 in
Weight	7 lb
Width	3.75 in

#### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277 V

#### Certifications and Compliance

Nema Rating	NEMA 3R
-------------	---------