



\* Representative image

## T153004

by Acme Electric  
Catalog ID: T153004

Low Voltage Distribution Transformer - Single Phase, 240X480 -  
120/240V, 0.05kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

|                      |                                   |
|----------------------|-----------------------------------|
| Construction         | Encapsulated                      |
| Max Temperature Rise | 115 Degrees Celsius               |
| Mounting Type        | Wall                              |
| Primary Voltage      | 240 X 480                         |
| Product Category     | Dry Type Distribution Transformer |
| Secondary Voltage    | 120/240 V                         |
| UL Insulation Class  | 130°C                             |
| UPC                  | 047503086285                      |
| Winding Material     | CU                                |
| kVA                  | 0.1                               |

### Dimensions

|        |         |
|--------|---------|
| Height | 6.41 in |
| Length | 3.05 in |
| Weight | 4 lb    |
| Width  | 3.14 in |

### Electrical Ratings

|                  |             |
|------------------|-------------|
| Frequency Rating | 50/60 Hz    |
| Primary Voltage  | 240 X 480 V |

### Certifications and Compliance

|              |              |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 3R      |
| UL Standard  | UL 506       |