



* Representative image

T153006

by Acme Electric
Catalog ID: T153006

Low Voltage Distribution Transformer - Single Phase, 240X480 -
120/240V, 0.15kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	130°C
UPC	047503085387
Winding Material	CU
kVA	0.1

Dimensions

Height	7.16 in
Length	3.67 in
Weight	7 lb
Width	3.89 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506