



* Representative image

T153105

by Acme Electric
Catalog ID: T153105

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V,
0.1kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	130°C
UPC	004750318330
Winding Material	CU
kVA	0.1

Dimensions

Height	7.16 in
Length	3.67 in
Weight	5 lb
Width	3.89 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506