



\* Representative image

# T179618S

by Acme Electric  
Catalog ID: T179618S

Low Voltage Lighting Transformer - Single Phase, 240 - 24V, 750VA

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

## Product Details

### General

Circuit Breaker Style	Push To Reset Thermal Breaker
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240
Product Category	Low Voltage Lighting Transformer
Secondary Voltage	24 V
UL Insulation Class	180°C
Winding Material	CU

### Dimensions

Height	11.68 in
Length	4.57 in
Weight	18 lb
Width	4.66 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

### Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 2
UL Standard	UL 506